



Pass and Seymour
TradeMaster® 1-Gang Nylon Wall Plate, Single Receptacle Opening, Brown
Part No. TP7



Trademaster Plate 1-Gang 1 Single Receptacle

Features & Benefits

Molded of rugged, practically indestructible self-extinguishing nylon. ('TP' series only.)

Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.

Nominal thickness, .070 inch.

Available in 'TP' series, extra 3/16 inch width and height than Standard size plates: and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates.

Preferred for hospital, industrial, institutional, and other high-abuse applications.

Specifications

General Info

| | | | |
|--------------------|-------------------------|-----------------|-------------------|
| Product Line | Pass & Seymour | Color | Brown |
| Finish | Matte | UPC Number | 785007274424 |
| Country Of Origin | United States | Construction | Plastic |
| Wall Plate Size | Standard Size | Wall Plate Type | Single Receptacle |
| Application Sector | Commercial, Residential | Standard | CSA, UL514 |
| Warranty Type | 1-Year Limited Warranty | Type | Wall Plate |

Dimensions

| | | | |
|------------------|-----------|------------------|---------|
| Product Width US | 2.9375 in | Product Depth US | 0.25 in |
|------------------|-----------|------------------|---------|

| | |
|-------------------|-----------|
| Product Height US | 4.6875 in |
|-------------------|-----------|

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 143222 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Additional Information

| | |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

Technical Information

| | | | |
|----------------|----------|-----------------|---------------|
| Thickness | 0.07 in | Number of Gangs | 1 |
| Indoor/Outdoor | Indoor | Mounting Type | Strap Mounted |
| Orientation | Vertical | | |