




Pass and Seymour  
Power Outlet Receptacle Openings, Two Gang, Brown  
Part No. TP703



Two Gang Power Outlet Receptacle Opening, 2.1563 hole for 2.125 diameter device - 4 mtg. holes, Light Almond Nylon.

## Features & Benefits

Molded of rugged, practically indestructible self-extinguishing nylon. ('TP' series only.)

Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.

Nominal thickness, .070 inch.

Available in 'TP' series, extra 3/16 inch width and height than Standard size plates: and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates.

Preferred for hospital, industrial, institutional, and other high-abuse applications.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Brown
Country Of Origin	Mexico	Wall Plate Type	Single Outlet
Application Sector	Residential/Commercial	Standard	CSA, UL514

### Dimensions

Product Width US	4.75 in	Product Depth US	0.25 in
Product Height US	4.6875 in		

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	143222	cULus Listed	Yes
---------------------	--------	--------------	-----

---

## Additional Information

---

Product Environmental Profile Yes

---

## Technical Information

---

Cutout	Power Outlet	Thickness	0.07 in
Number of Gangs	2	Mounting Type	Exposed Screws

---