



Pass and Seymour  
TradeMaster® 2-Gang Nylon Wall Plate, 2.1563-in Power Outlet Receptacle Opening, 4 Mtg Holes, Gray  
Part No. TP703GRY



Two Gang Power Outlet Receptacle Opening, 2.1563 hole for 2.125 diameter device - 4 mtg. holes, Light Almond Nylon.

## Features & Benefits

Molded of rugged, practically indestructible self-extinguishing nylon. ('TP' series only.) Available in 'TP' series, extra 3/16 inch width and height than Standard size plates: and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates.

Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond. Preferred for hospital, industrial, institutional, and other high-abuse applications.

Nominal thickness, .070 inch.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Gray
Finish	Matte	UPC Number	785007275834
Country Of Origin	Mexico	Construction	Plastic
Wall Plate Size	Standard Size	Wall Plate Type	Outlet, Round
Application Sector	Commercial, Residential	Standard	CSA, UL514
Warranty Type	1-Year Limited Warranty	Type	Wall Plate

### Dimensions

Product Width US	4.75 in	Product Depth US	0.25 in
Product Height US	4.6875 in	Circular Outlet Diameter	2.1563 mm

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	143222	cULus Listed	Yes
---------------------	--------	--------------	-----

Additional Information

Product Environmental Profile      Yes

Technical Information

Thickness	0.07 in	Number of Gangs	2
Indoor/Outdoor	Indoor	Mounting Type	Strap Mounted
Orientation	Vertical		