



Pass and Seymour
Power Outlet Receptacle Openings, Two Gang, Gray
Part No. TP703GRY



Two Gang Power Outlet Receptacle Opening, 2.1563 hole for 2.125 diameter device - 4 mtg. holes, Light Almond Nylon.

Features & Benefits

Molded of rugged, practically indestructible self-extinguishing nylon. ('TP' series only.)

Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.

Nominal thickness, .070 inch.

Available in 'TP' series, extra 3/16 inch width and height than Standard size plates: and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates.

Preferred for hospital, industrial, institutional, and other high-abuse applications.

Specifications

General Info

| | | | |
|--------------------|------------------------|-----------------|---------------|
| Product Line | Pass & Seymour | Color | Gray |
| Country Of Origin | Mexico | Wall Plate Type | Single Outlet |
| Application Sector | Residential/Commercial | Standard | CSA, UL514 |

Dimensions

| | | | |
|-------------------|-----------|------------------|---------|
| Product Width US | 4.75 in | Product Depth US | 0.25 in |
| Product Height US | 4.6875 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 143222 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Additional Information

Product Environmental Profile Yes

Technical Information

| | | | |
|-----------------|--------------|---------------|----------------|
| Cutout | Power Outlet | Thickness | 0.07 in |
| Number of Gangs | 2 | Mounting Type | Exposed Screws |
