



Pass and Seymour  
TradeMaster® 2-Gang Nylon Wall Plate, 2.1563-in Power Outlet Receptacle Opening, 4 Mtg Holes, Light Almond  
Part No. TP703LA



Two Gang Power Outlet Receptacle Opening, 2.1563 hole for 2.125 diameter device - 4 mtg. holes,Light AlmondNylon.

Features & Benefits

- Molded of rugged, practically indestructible self-extinguishing nylon. ('TP' series only.)
- Available in 'TP' series, extra 3/16 inch width and height than Standard size plates: and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates.
- Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.
- Preferred for hospital, industrial, institutional, and other high-abuse applications.
- Nominal thickness, .070 inch.

Specifications

General Info			
Product Line	Pass & Seymour	Color	Light Almond
Finish	Matte	UPC Number	785007275858
Country Of Origin	Mexico	Construction	Plastic
Wall Plate Size	Standard Size	Wall Plate Type	Outlet, Round
Application Sector	Commercial, Residential	Standard	CSA, UL514
Warranty Type	1-Year Limited Warranty	Type	Wall Plate
Dimensions			
Product Width US	4.75 in	Product Depth US	0.25 in
Product Height US	4.6875 in	Circular Outlet Diameter	2.1563 mm
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	143222	cULus Listed	Yes
Additional Information			
Product Environmental Profile	Yes		

Technical Information

Thickness	0.07 in	Number of Gangs	2
Indoor/Outdoor	Indoor	Mounting Type	Strap Mounted
Orientation	Vertical		