



Pass and Seymour
Power Outlet Receptacle Openings, One Gang, Black
Part No. TP724BK



OneGang Power Outlet Receptacle Opening, 2.156 hole for 2.125 diameter device -2 mtg. holes,White Nylon.

Features & Benefits

Molded of rugged, practically indestructible self-extinguishing nylon. ('TP' series only.)

Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.

Nominal thickness, .070 inch.

Available in 'TP' series, extra 3/16 inch width and height than Standard size plates: and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates.

Preferred for hospital, industrial, institutional, and other high-abuse applications.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	Mexico	Wall Plate Type	Single Outlet
Application Sector	Residential/Commercial	Standard	CSA, UL514

Dimensions

Product Width US	2.9375 in	Product Depth US	0.25 in
Product Height US	4.6875 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

Product Environmental Profile Yes

Technical Information

Cutout	Power Outlet	Thickness	0.07 in
Number of Gangs	1	Mounting Type	Exposed Screws
