



Pass and Seymour
Combination Openings, 1 Toggle Switch and 1 Decorator, Two Gang, Light Almond
Part No. TPJ126LA



Combination Wall Plate, 1 Toggle Switch and 1 Decorator, 2-Gang

Features & Benefits

Molded of rugged, practically indestructible self-extinguishing nylon. ('TP' series only.)

Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.

Nominal thickness, .070 inch.

Available in 'TP' series, extra 3/16 inch width and height than Standard size plates: and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates.

Preferred for hospital, industrial, institutional, and other high-abuse applications.

Specifications

General Info

| | | | |
|--------------------|---------------------------|-----------------|---------------------------------------|
| Product Line | Pass & Seymour | Color | Light Almond |
| Finish | Matte | UPC Number | 785007025729 |
| Country Of Origin | Mexico | Wall Plate Type | Combination, Decorator, Toggle Switch |
| Application Sector | Commercial, Residential | Standard | CSA, UL514 |
| Warranty Type | Limited Lifetime Warranty | Type | Wall Plate |

Dimensions

| | | | |
|-------------------|-----------|------------------|---------|
| Product Width US | 5.125 in | Product Depth US | 0.25 in |
| Product Height US | 5.0625 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 143222 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Additional Information

| | |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

Technical Information

| | | | |
|--------|----------------------|-----------|---------|
| Cutout | Toggle and Decorator | Thickness | 0.07 in |
|--------|----------------------|-----------|---------|

| | | | |
|-----------------|---|----------------|--------|
| Number of Gangs | 2 | Indoor/Outdoor | Indoor |
|-----------------|---|----------------|--------|

| | |
|-------------|------------|
| Orientation | Horizontal |
|-------------|------------|