



Trademaster Wall Plate Jumbo 2-gang 1-toggle 1-duplex receptacle

## Features & Benefits

Molded of rugged, practically indestructible self-extinguishing nylon. ('TP' series only.)

High Impact resistant nylon face.

Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.

Preferred for hospital, industrial, institutional, and other high-abuse applications.

Nominal thickness, .070 inch.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Ivory
Country Of Origin	Mexico	Wall Plate Type	Combination, Dimmer/Switch, Outlet
Application Sector	Residential/Commercial	Standard	CSA, UL514

### Dimensions

Product Width US	5.125 in	Product Depth US	0.25 in
Product Height US	5.0625 in		

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	143222	cULus Listed	Yes
---------------------	--------	--------------	-----

### Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

---

## Technical Information

---

Cutout	Toggle and Receptacle	Thickness	0.07 in
Number of Gangs	2	Mounting Type	Exposed Screws

---