



Pass and Seymour  
TradeMaster® Junior Jumbo 2-Gang Nylon Wall Plate, 2 Decorator Openings, Light Almond  
Part No. TPJ262LA



Trademaster Wall Plate Jumbo 2-Gang 2-Decorator

## Features & Benefits

Molded of rugged, practically indestructible self-extinguishing nylon. ('TP' series only.) Available in 'TP' series, extra 3/16 inch width and height than Standard size plates: and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates.

Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond. Preferred for hospital, industrial, institutional, and other high-abuse applications.

Nominal thickness, .070 inch.

## Specifications

### General Info

|                    |                          |                 |              |
|--------------------|--------------------------|-----------------|--------------|
| Product Line       | Pass & Seymour           | Color           | Light Almond |
| Finish             | Matte                    | UPC Number      | 785007025477 |
| Country Of Origin  | Mexico                   | Construction    | Plastic      |
| Wall Plate Size    | Trademaster Junior-Jumbo | Wall Plate Type | Decorator    |
| Application Sector | Commercial, Residential  | Standard        | CSA, UL514   |
| Warranty Type      | 1-Year Limited Warranty  | Type            | Wall Plate   |

### Dimensions

|                   |           |                  |         |
|-------------------|-----------|------------------|---------|
| Product Width US  | 5.125 in  | Product Depth US | 0.25 in |
| Product Height US | 5.0625 in |                  |         |

### Listing Agencies / 3rd Party Agencies

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 143222 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Additional Information

|                               |     |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

Technical Information

|                |          |                 |             |
|----------------|----------|-----------------|-------------|
| Thickness      | 0.07 in  | Number of Gangs | 2           |
| Indoor/Outdoor | Indoor   | Mounting Type   | Box Mounted |
| Orientation    | Vertical |                 |             |