




Pass and Seymour  
Toggle Switch Openings, Three Gang, Ivory  
Part No. TPJ3I



Trademaster Wall Plate Jumbo 3 Gang 3 Toggle

## Features & Benefits

Molded of rugged, practically indestructible self-extinguishing nylon. ('TP' series only.)

Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.

Nominal thickness, .070 inch.

Available in 'TP' series, extra 3/16 inch width and height than Standard size plates: and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates.

Preferred for hospital, industrial, institutional, and other high-abuse applications.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

|                    |                        |                 |               |
|--------------------|------------------------|-----------------|---------------|
| Product Line       | Pass & Seymour         | Color           | Ivory         |
| Country Of Origin  | Mexico                 | Wall Plate Type | Dimmer/Switch |
| Application Sector | Residential/Commercial | Standard        | CSA, UL514    |

### Dimensions

|                   |           |                  |         |
|-------------------|-----------|------------------|---------|
| Product Width US  | 6.9375 in | Product Depth US | 0.25 in |
| Product Height US | 5.0625 in |                  |         |

### Listing Agencies / 3rd Party Agencies

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 143222 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

---

## Additional Information

---

Product Environmental Profile Yes

---

## Technical Information

---

|                 |        |               |                |
|-----------------|--------|---------------|----------------|
| Cutout          | Toggle | Thickness     | 0.07 in        |
| Number of Gangs | 3      | Mounting Type | Exposed Screws |

---