



Pass and Seymour  
**15A 125V Hospital-Grade Tamper-Resistant Duplex Receptacle with USB C/C Fast Charging Ports, Black**  
Part No. TR15HUSBCC6BK



15A 125A Hospital Grade Tamper-Resistant REC+2 USBC FAST CHR6

## Specifications

### General Info

Product Line	Pass & Seymour	Country Of Origin	China
--------------	----------------	-------------------	-------

### Dimensions

Product Width US	1.693 in	Product Depth US	1.425 in
Product Height US	2.677 in		

### Technical Information

USB Amperage	6 A	Number of USBs	2
USB Power Output	15 W	Amperage	15 A