



Pass and Seymour
15W Spec Grade USB Outlet, Type A/C, 15A, Tamper-Resistant, Black
Part No. TR15USBAC6BK



Combination Tamper-Resistant 15A Duplex Convenience
Receptacles with two fast charging 6A USB ports Type A and C

Features & Benefits

Protects children: patented shutter system helps prevent improper insertion of foreign objects

Meets National
Electrical Code®
Tamper Resistant
requirement

Conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the indicator light flashes to signal that the GFCI should be replaced. It also has our proven SafeLock® Protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected

High-impact-resistant
thermoplastic
construction with tri-
drive terminal screws

High-impact-resistant thermoplastic construction with tri-drive terminal screws.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Finish	Matte	UPC Number	785007209716
Country Of Origin	China	Number of Receptacles	2
Features	USB-A Charging, USB-C Charging	Outlet Type	Tamper-Resistant, USB-Charging
Application Sector	Commercial, Residential	Type	Outlet

Dimensions

Product Width US	1.693 in	Product Depth US	1.425 in
------------------	----------	------------------	----------

Product Height US	2.677 in
-------------------	----------

Technical Information

USB Amperage	6 A	Number of USBs	2
USB Power Output	15 W	Amperage	15 A
Number of Poles	Double Pole	Indoor/Outdoor	Indoor