




Pass and Seymour
3.1A Spec Grade USB Outlet, Type A/C, 15A, Tamper-Resistant, Ivory
Part No. TR15USBACI



Combination Tamper-Resistant 15A Duplex Convenience
Receptacles with two 3.1A USB charging ports Type A and C

Features & Benefits

Protects children: patented shutter system helps prevent improper insertion of foreign objects

Meets National
Electrical Code®
Tamper-Resistant
requirement

Conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the indicator light flashes to signal that the GFCI should be replaced. It also has our proven SafeLock® Protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected

High-impact-resistant
thermoplastic
construction with tri-
drive terminal screws

High-impact-resistant thermoplastic construction with tri-drive terminal screws.

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
UPC Number	785007181494	Country Of Origin	China
Number of Receptacles	2	Features	USB-A Charging, USB-C Charging
Outlet Type	Tamper-Resistant, USB-Charging	Application Sector	Commercial, Residential
Standard	FEDSPEC	Type	Outlet

Dimensions

Product Width US	1.693 in	Product Depth US	1.425 in
------------------	----------	------------------	----------

Product Height US	2.677 in
-------------------	----------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

USB Amperage	3.1 A	Number of USBs	2
--------------	-------	----------------	---

USB Power Output	15 W	Amperage	15 A
------------------	------	----------	------

Number of Poles	Double Pole	Indoor/Outdoor	Indoor
-----------------	-------------	----------------	--------