



Pass and Seymour  
3.1A Spec Grade USB Outlet, Type A/C, 15A, Tamper-Resistant, White  
Part No. TR15USBACW



Combination Tamper-Resistant 15A Duplex Convenience  
Receptacles with two 3.1A USB charging ports Type A and C

## Features & Benefits

Protects children: patented shutter system helps prevent improper insertion of foreign objects

Meets National  
Electrical Code®  
Tamper-Resistant  
requirement

Conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the indicator light flashes to signal that the GFCI should be replaced. It also has our proven SafeLock® Protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected

High-impact-resistant  
thermoplastic  
construction with tri-  
drive terminal screws

High-impact-resistant thermoplastic construction with tri-drive terminal screws.

## Specifications

### General Info

|                    |                                |                       |                                |
|--------------------|--------------------------------|-----------------------|--------------------------------|
| Product Line       | Pass & Seymour                 | Color                 | White                          |
| Finish             | Matte                          | UPC Number            | 785007181531                   |
| Country Of Origin  | Vietnam                        | Number of Receptacles | 2                              |
| Features           | USB-A Charging, USB-C Charging | Outlet Type           | Tamper-Resistant, USB-Charging |
| Application Sector | Commercial, Residential        | Standard              | FEDSPEC                        |
| Type               | Outlet                         |                       |                                |

### Dimensions

|                  |          |                  |          |
|------------------|----------|------------------|----------|
| Product Width US | 1.693 in | Product Depth US | 1.425 in |
|------------------|----------|------------------|----------|

|                   |          |
|-------------------|----------|
| Product Height US | 2.677 in |
|-------------------|----------|

Listing Agencies / 3rd Party Agencies

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Additional Information

|                               |     |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

Technical Information

|              |       |                |   |
|--------------|-------|----------------|---|
| USB Amperage | 3.1 A | Number of USBs | 2 |
|--------------|-------|----------------|---|

|                  |      |          |      |
|------------------|------|----------|------|
| USB Power Output | 15 W | Amperage | 15 A |
|------------------|------|----------|------|

|                 |             |                |        |
|-----------------|-------------|----------------|--------|
| Number of Poles | Double Pole | Indoor/Outdoor | Indoor |
|-----------------|-------------|----------------|--------|