



Pass and Seymour
15W Spec Grade USB Outlet, Type C, 15A, Tamper-Resistant, Gray
Part No. TR15USBC66GRY



Heavy-Duty Decorator Specification Grade USB Charging Receptacles
15A, 125V

Features & Benefits

Overall 6A charging capability with smart current-sharing technology to allow for full 3A through a singular Type-C port

Posted terminal screws and external back-wire pressure plates for more productive and reliable terminations

With (2) USB Type-C ports to charge the latest mobile devices

USB Type-C ports carry a minimum rating of 10,000 insertions

Stainless steel auto-ground clips assure positive ground

Slim design allows for installation in standard depth wall boxes

Multiple color options available

Efficient power supply meets the Department of Energy (DoE) Level VI no-load power requirement of 100mW max for external power supplies

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007209785
Country Of Origin	China		

Dimensions

Product Width US	1.693 in	Product Depth US	1.425 in
Product Height US	2.677 in		

Technical Information

Amperage	15 A
----------	------