



Pass and Seymour
15W Spec Grade USB Outlet, Type C, 15A, Tamper-Resistant, Ivory
Part No. TR15USBC6I



Heavy-Duty Decorator Specification Grade USB Charging Receptacles
15A, 125V

Features & Benefits

Overall 6A charging capability with smart current-sharing technology to allow for full 3A through a singular Type-C port	Posted terminal screws and external back-wire pressure plates for more productive and reliable terminations
With (2) USB Type-C ports to charge the latest mobile devices	USB Type-C ports carry a minimum rating of 10,000 insertions
Stainless steel auto-ground clips assure positive ground	Slim design allows for installation in standard depth wall boxes
Multiple color options available	Efficient power supply meets the Department of Energy (DoE) Level VI no-load power requirement of 100mW max for external power supplies

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007209792
Country Of Origin	China		

Dimensions

Product Width US	1.693 in	Product Depth US	1.425 in
Product Height US	2.677 in		

Technical Information

Amperage	15 A
----------	------