



Pass and Seymour  
15W Spec Grade USB Outlet, Type C, 15A, Tamper-Resistant, Light Almond  
Part No. TR15USBC6LA



Heavy-Duty Decorator Specification Grade USB Charging Receptacles 15A, 125V

## Features & Benefits

Overall 6A charging capability with smart current-sharing technology to allow for full 3A through a singular Type-C port	Posted terminal screws and external back-wire pressure plates for more productive and reliable terminations
With (2) USB Type-C ports to charge the latest mobile devices	USB Type-C ports carry a minimum rating of 10,000 insertions
Stainless steel auto-ground clips assure positive ground	Slim design allows for installation in standard depth wall boxes
Multiple color options available	Efficient power supply meets the Department of Energy (DoE) Level VI no-load power requirement of 100mW max for external power supplies

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Light Almond
UPC Number	785007209808	Country Of Origin	China
Number of Receptacles	2	Features	USB-C Charging
Outlet Type	Tamper-Resistant, USB-Charging	Application Sector	Commercial, Multi-Dwelling Unit, Residential
Wall Plate Included	No	Warranty Type	1-Year Limited Warranty

### Dimensions

Product Width US	1.693 in	Product Depth US	1.425 in
------------------	----------	------------------	----------

Product Height US	2.677 in
-------------------	----------

Technical Information

Is Tamper-Resistant	Yes	Connection Location	Side Only
USB Amperage	6 A	Number of USBs	2
Number of Wires	3	Number of Gangs	1
Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
NEMA Configuration Code	5-15R	Wire Connection Type	Screw Terminals
Voltage	125.0 V		