



Pass and Seymour  
20A 125V Hospital-Grade Tamper-Resistant Receptacle with USB A/C Charging Ports, Brown  
Part No. TR20HUSBAC



20A 125V Hospital Grade Tamper-Resistant Receptacle with two 3.1A USB charging ports  
Type A and C

## Features & Benefits

High Impact resistant nylon face.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Brown
Country Of Origin	China	Number of Receptacles	2
Features	USB-A Charging, USB-C Charging	Outlet Type	Commercial, Indoor, Tamper-Resistant, USB-Charging
Type	Outlet		

### Dimensions

Product Width US	1.693 in	Product Depth US	1.425 in
Product Height US	2.677 in		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

### Technical Information

---

USB Amperage	3.1 A	Number of USBs	2
USB Power Output	15 W	Amperage	20 A
Number of Poles	Double Pole	Indoor/Outdoor	Indoor
Voltage	125.0 V		

---