



Pass and Seymour  
20A 125V Hospital-Grade Tamper-Resistant Receptacle with USB A/C Fast Charging Ports, Light Almond  
Part No. TR20HUSBAC6LA



20A 125V Hospital Grade Tamper-Resistant REC+USBA+C FAST CHR

## Specifications

### General Info

Product Line	Pass & Seymour	Country Of Origin	China
--------------	----------------	-------------------	-------

### Dimensions

Product Width US	1.693 in	Product Depth US	1.425 in
Product Height US	2.677 in		

### Technical Information

USB Amperage	6 A	Number of USBs	2
USB Power Output	15 W	Amperage	20 A