



Pass and Seymour  
20A 125V Tamper-Resistant Duplex Receptacle with USB A/C Fast Charging Ports, Black  
Part No. TR20USBAC6BK



20A 125V Tamper-Resistant Receptacle with two 6A USB fast charging ports Type A and C

## Features & Benefits

High Impact resistant nylon face.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
Finish	Matte	Country Of Origin	China
Number of Receptacles	2	Features	USB-A Charging, USB-C Charging
Outlet Type	Commercial, Indoor, Residential, Tamper-Resistant, USB-Charging	Warranty Type	1-Year Limited Warranty
Type	Outlet		

### Dimensions

Product Width US	1.693 in	Product Depth US	1.425 in
Product Height US	2.677 in		

### Technical Information

USB Amperage	6 A	Number of USBs	2
--------------	-----	----------------	---

---

USB Power Output	30 W	Amperage	20 A
Number of Poles	Double Pole	Indoor/Outdoor	Indoor
Voltage	125.0 V		

---