



Pass and Seymour
20A 125V Tamper-Resistant Duplex Receptacle with USB A/C Fast Charging Ports, Red
Part No. TR20USBAC6RED



20A 125V Tamper-Resistant Receptacle with two 6A USB fast charging ports Type A and C

Features & Benefits

High Impact resistant nylon face.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	China
Number of Receptacles	2	Features	USB-A Charging, USB-C Charging
Outlet Type	Commercial, Indoor, Residential, Tamper-Resistant, USB-Charging	Warranty Type	1-Year Limited Warranty
Type	Outlet		

Dimensions

Product Width US	1.693 in	Product Depth US	1.425 in
Product Height US	2.677 in		

Technical Information

Is Tamper-Resistant	Yes	USB Amperage	6 A
Number of USBs	2	USB Power Output	30 W
Amperage	20 A	Number of Poles	Double Pole

Indoor/Outdoor

Indoor

Voltage

125.0 V
