



Pass and Seymour
20A 125V Tamper-Resistant Duplex Receptacle with USB A/C Charging Ports, Gray
Part No. TR20USBACGRY



20A 125V Tamper-Resistant Receptacle with two 3.1A USB charging ports Type A and C

Features & Benefits

Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Finish	Matte	Country Of Origin	China
Number of Receptacles	2	Features	USB-A Charging, USB-C Charging
Outlet Type	Commercial, Indoor, Residential, Tamper-Resistant, USB-Charging	Type	Outlet

Dimensions

Product Width US	1.693 in	Product Depth US	1.425 in
Product Height US	2.677 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

Product Environmental Profile Yes

Technical Information

USB Amperage	3.1 A	Number of USBs	2
USB Power Output	15 W	Amperage	20 A
Number of Poles	Double Pole	Indoor/Outdoor	Indoor
Voltage	125.0 V		
