



Pass and Seymour

15A 125V Spec-Grade Tamper-Resistant Decorator Duplex Receptacle, Back and Side Wire, Black

Part No. TR26252BK



Tamper-Resistant Decorator Spec Grade Receptacle, Back & Side Wire, 15amp 125volt, Black

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles page](#).

## Features & Benefits

Dual mechanical shutter system to help prevent insertion of foreign objects.

AC receptacles available in 15 and 20A, 125V.

Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.

High impact-resistant nylon face and thermoplastic back body.

Back and side wire capability

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	Mexico	Number of Receptacles	2
Outlet Type	Commercial, Indoor, Tamper-Resistant	Warranty Type	1-Year Limited Warranty
Type	Outlet		

### Dimensions

Product Width US	1.37 in	Product Depth US	0.93 in
Product Height US	3.28 in		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Technical Information

---

Is Tamper-Resistant Yes

Amperage

15 A

---

Number of Poles Double Pole

Indoor/Outdoor

Indoor

---

Voltage 125.0 V

---