



Tamper-Resistant Decorator Spec Grade Receptacle, Back & Side Wire, 15amp 125volt, Black

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles page](#).

### Features & Benefits

Dual mechanical shutter system to help prevent insertion of foreign objects.	AC receptacles available in 15 and 20A, 125V.
Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.	High impact-resistant nylon face and thermoplastic back body.
Back and side wire capability	For covering patents, see <a href="http://www.legrand.us/patents">www.legrand.us/patents</a> .

### Specifications

#### General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	Mexico	Number of Receptacles	2
Outlet Type	Commercial, Indoor, Tamper-Resistant	Warranty Type	1-Year Limited Warranty
Type	Outlet		

#### Dimensions

Product Width US	1.37 in	Product Depth US	0.93 in
Product Height US	3.28 in		

#### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

#### Technical Information

Is Tamper-Resistant	Yes	Amperage	15 A
Number of Poles	Double Pole	Indoor/Outdoor	Indoor
Voltage	125.0 V		