



Pass and Seymour
Heavy Duty Decorator Spec Grade 15A Plug Load Controllable Receptacle, Light Almond
Part No. TR26262CDLA



This durable, dependable Plug Load receptacle is designed to help you meet ASHRAE energy standards. The controlled marking printed on the tough nylon face is both NEMA-approved and compliant with the National Electrical Code.

Features & Benefits

- Permanent controlled receptacle markings using abrasion resistant ink.

Can be wired to any number of stand-alone or system-based plug load control solutions.

Tri-drive brass-plated terminal screws. Two back-wire holes for more wiring flexibility.

Two drive screws anchor strap to back body and face where abrupt removal torque is strongest.

Auto-ground eliminates the necessity to terminate grounding conductor in device.

For covering patents, see www.legrand.us/patents.
- Controlled receptacle marking is NEMA-approved and compliant with 2014 NEC, CA Title 24, and ASHRAE Energy Efficiency Standard 90.1.

CH Version Only: Split circuit tab broken at the factory, allowing half of the receptacle to be controlled.

.032 inch thick, brass, triple-wipe power contacts for lasting retention.

Corrosion-resistant, plated steel strap locked into face and back body to resist pulling away from face/body assembly.

Dual mechanical shutter system to help prevent insertion of foreign objects (in Tamper-Resistant models).

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	Light Almond
UPC Number	785007051162	Country Of Origin	Mexico
Standard	FEDSPEC		

Dimensions

Product Width US	1.322 in	Product Depth US	0.78 in
------------------	----------	------------------	---------

Product Height US	2.635 in
-------------------	----------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Amperage	15 A
----------	------
