



Pass and Seymour  
20A 125V Spec-Grade Tamper-Resistant Decorator Duplex Receptacle, Side Wire, Brown  
Part No. TR26342



Tamper-Resistant Decorator Spec Grade Receptacle, Side Wire Only, 20A, 125V

Features & Benefits

Dual mechanical shutter system to help prevent insertions of foreign objects.	AC receptacles available in 15 and 20A, 125V.
Auto-ground clip assures positive ground.	Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.
Backed-out tri-drive steel terminal screws. Side wire only.	For covering patents, see <a href="http://www.legrand.us/patents">www.legrand.us/patents</a> .

Specifications

General Info

Product Line	Pass & Seymour	Color	Brown
UPC Number	785007034905	Country Of Origin	Mexico
Number of Receptacles	2	Outlet Type	Tamper-Resistant
Application Sector	Commercial	Type	Outlet

Dimensions

Product Width US	1.37 in	Product Depth US	0.93 in
Product Height US	3.28 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Is Tamper-Resistant	Yes	Amperage	20 A
Number of Poles	Double Pole	Indoor/Outdoor	Indoor