



Pass and Seymour
20A 125V Spec-Grade Tamper-Resistant Decorator Duplex Receptacle, Side Wire, Ivory
Part No. TR26342I



Tamper-Resistant Decorator Spec Grade Receptacle, Side Wire Only, 20A, 125V

Features & Benefits

Dual mechanical shutter system to help prevent insertions of foreign objects.

Auto-ground clip assures positive ground.

Backed-out tri-drive steel terminal screws. Side wire only.

AC receptacles available in 15 and 20A, 125V.

Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Country Of Origin	Mexico	Number of Receptacles	2
Outlet Type	Commercial, Indoor, Tamper-Resistant	Type	Outlet

Dimensions

Product Width US	1.37 in	Product Depth US	0.93 in
Product Height US	3.28 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Is Tamper-Resistant	Yes	Amperage	20 A
---------------------	-----	----------	------

Number of Poles	Double Pole	Indoor/Outdoor	Indoor
-----------------	-------------	----------------	--------

Voltage	125.0 V
---------	---------
