



Tamper-Resistant Construction Spec Grade Single Receptacles, Back and Side Wire, 15A, 125V

Features & Benefits

Dual mechanical shutter system to help prevent insertions of foreign objects.

.032 inch thick brass triple-wipe power contacts for lasting retention.

Auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Corrosion-resistant, plated and tabbed steel strap locked in to face and back body to resist pulling away from face/body assembly.

Corrosion-resistant plated steel strap is locked in to the face and back body to resist pulling away from the face/body assembly.

Easily accessed break-off line-contact connecting tab for fast and easy split-circuitwiring.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007241983
Country Of Origin	Mexico	Number of Receptacles	1
Outlet Type	Tamper-Resistant	Application Sector	Commercial
Warranty Type	1-Year Limited Warranty	Type	Outlet

Dimensions

Product Width US	1.38 in	Product Depth US	1.19 in
Product Height US	3.28 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	140596	cULus Listed	Yes
Technical Information			
Is Tamper-Resistant	Yes	Amperage	15 A
Number of Poles	Double Pole	Indoor/Outdoor	Indoor