



**Pass and Seymour**  
**15A 125V Spec-Grade Tamper-Resistant Duplex Receptacle, Back and Side Wire, Gray**  
Part No. TR5252GRY



Tamper-Resistant Specification Grade Duplex Receptacle, Back and Side Wire, 15A, 125V. Available in 6 colors. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

## Features & Benefits

Dual mechanical shutter system to help prevent insertion of foreign objects.

Auto-ground clip assures positive ground.

Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.

High impact-resistant nylon face and thermoplastic back body.

Back and side wire capability

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Gray
Country Of Origin	Mexico	Number of Receptacles	2
Outlet Type	Commercial, Indoor, Tamper-Resistant	Type	Outlet

### Dimensions

Product Width US	1.37 in	Product Depth US	0.93 in
Product Height US	3.28 in		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

---

## Technical Information

---

Is Tamper-Resistant	Yes	Amperage	15 A
---------------------	-----	----------	------

---

Number of Poles	Double Pole	Indoor/Outdoor	Indoor
-----------------	-------------	----------------	--------

---

Voltage	125.0 V
---------	---------

---