



Pass and Seymour  
15A 125V Spec-Grade Tamper-Resistant Duplex Receptacle, Back and Side Wire, Ivory  
Part No. TR5252I



Tamper-Resistant Specification Grade Duplex Receptacle, Back and Side Wire, 15A, 125V. Available in 6 colors. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

Dual mechanical shutter system to help prevent insertion of foreign objects.	Auto-ground clip assures positive ground.
Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.	High impact-resistant nylon face and thermoplastic back body.
Back and side wire capability	For covering patents, see <a href="http://www.legrand.us/patents">www.legrand.us/patents</a> .

Specifications

General Info			
Product Line	Pass & Seymour	Color	Ivory
Country Of Origin	Mexico	Number of Receptacles	2
Outlet Type	Commercial, Indoor, Tamper-Resistant	Type	Outlet
Dimensions			
Product Width US	1.37 in	Product Depth US	0.93 in
Product Height US	3.28 in	Product Length US	4.0E-4 in
Listing Agencies / 3rd Party Agencies			
cULus Listed	Yes		

Technical Information

---

Is Tamper-Resistant	Yes	Amperage	15 A
Number of Poles	Double Pole	Indoor/Outdoor	Indoor
Voltage	125.0 V		

---