



Pass and Seymour  
15A 125V Spec-Grade Tamper-Resistant Duplex Receptacle, Back and Side Wire, White  
Part No. TR5252W



Tamper-Resistant Specification Grade Duplex Receptacle, Back and Side Wire, 15A, 125V.  
Available in 6 colors. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

## Features & Benefits

Dual mechanical shutter system to help prevent insertion of foreign objects.

Auto-ground clip assures positive ground.

Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.

High impact-resistant nylon face and thermoplastic back body.

Back and side wire capability

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007034646
Country Of Origin	Mexico	Number of Receptacles	2
Outlet Type	Tamper-Resistant	Application Sector	Commercial
Type	Outlet		

### Dimensions

Product Width US	1.37 in	Product Depth US	0.93 in
Product Height US	3.28 in	Product Length US	1.0E-4 in

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Is Tamper-Resistant	Yes	Amperage	15 A
Number of Poles	Double Pole	Indoor/Outdoor	Indoor