



Tamper-Resistant Extra Heavy-Duty Surge Protective Duplex Receptacle offers increased transient protection, reliability and protection notification (Audible Alarm with LED Indicator). Back and Side Wire, 15amp 125volt, White. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

Dual mechanical shutter system to help prevent insertion of foreign objects.	Auto-ground clip assures positive ground.
Backed-out tri-drive brass terminal screws for faster installation.	Internal screw-pressure-plate back and side wire capability.
Two back wire holes for additional wiring flexibility.	Corrosion-resistant plated steel strap is locked in to face and back body to resist pulling away from the face/body assembly.
.032 inch thick brass triple-wipe power contacts.	Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest.
For covering patents, see www.legrand.us/patents .	

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	China
Application Sector	Residential/Commercial		

Dimensions

Product Width US	1.7 in	Product Depth US	1.4 in
Product Height US	2.75 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Phase	Single	Frequency Rating	60 Hz
Connection	Side & Back Wire	Class	IG
Amperage	15 A	Type of Indicators	LED, Audible Alarm
Voltage	125.0 V	Environmental Conditions	UL94 V2