




Pass and Seymour  
Hard-Use Spec Grade Plug Load Controllable Receptacle, 15A, 125V, Gray  
Part No. TR5262CDGRY



Permanent controlled receptacle marking allows for long-lasting, easy identification of controlled receptacle for end-users. NEMA-approved and compliant with NEC, CA Title 24, and ASHRAE Energy Efficiency Standard 90.1.

## Features & Benefits

Can be wired to any number of system-based or stand-alone plug load control solutions.	Corrosion-resistant, plated and tabbed steel strap locked in to face and back body to resist pulling away from face/body assembly.
.032 inch thick, brass, triple-wipe power contacts for lasting retention.	Permanent controlled receptacle markings using abrasion resistant ink.
Two drive screws anchor strap to back body and face where abrupt removal torque is strongest.	Tri-drive brass-plated terminal screws. Two back-wire holes for more wiring flexibility.
Dual mechanical shutter system to help prevent insertion of foreign objects (for Tamper-Resistant models).	Strap tabs wrap around face to prevent strap from separating from face and back body.
CH Version Only: Split circuit tab broken at the factory, allowing half of the receptacle to be controlled.	For covering patents, see <a href="http://www.legrand.us/patents">www.legrand.us/patents</a> .
For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, <a href="#">click here</a> .	

## Specifications

### General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
--------------	----------------	-------------------	--------

### Dimensions

Product Width US	1.322 in	Product Depth US	0.78 in
Product Height US	2.63 in		

---

Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

---

Technical Information

---

Amperage	15 A
----------	------

---