



Pass and Seymour  
**Tamper-Resistant Extra Heavy Duty Surge Protective Duplex Receptacle, Ivory**  
Part No. TR5262ISP



Tamper-Resistant Extra Heavy-Duty Surge Protective Duplex Receptacle offers increased transient protection, reliability and protection notification (Audible Alarm with LED Indicator). Back and Side Wire, 15amp 125volt, White. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

## Features & Benefits

Dual mechanical shutter system to help prevent insertion of foreign objects.

Auto-ground clip assures positive ground.

Backed-out tri-drive brass terminal screws for faster installation.

Internal screw-pressure-plate back and side wire capability.

Two back wire holes for additional wiring flexibility.

Corrosion-resistant plated steel strap is locked in to face and back body to resist pulling away from the face/body assembly.

.032 inch thick brass triple-ripe power contacts.

Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	UPC Number	785007020915
Country Of Origin	China	Application Sector	Commercial, Residential

### Dimensions

Product Width US	1.7 in	Product Depth US	1.4 in
Product Height US	2.75 in		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Phase	Single	Connection	Side & Back Wire
Class	IG	Amperage	15 A
Type of Indicators	Audible Alarm, LED	Environmental Conditions	UL94 V2