



Pass and Seymour
20A 125V Specification Grade Tamper-Resistant Duplex Receptacle, Back and Side Wire, Brown
Part No. TR5352



Tamper-Resistant Specification Grade Duplex Receptacle, Back and Side Wire, 20A, 125V. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

Dual mechanical shutter system to help prevent insertion of foreign objects. AC receptacles available in 15 and 20A, 125V.

Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring. High impact-resistant nylon face and thermoplastic back body.

Back and side wire capability

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Brown
UPC Number	785007034684	Country Of Origin	Mexico
Number of Receptacles	2	Outlet Type	Tamper-Resistant
Application Sector	Commercial	Type	Outlet

Dimensions

Product Width US	1.37 in	Product Depth US	0.93 in
Product Height US	3.28 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Is Tamper-Resistant	Yes	Amperage	20 A
Number of Poles	Double Pole	Indoor/Outdoor	Indoor