




Pass and Seymour  
**20A 125V Hard Use Spec-Grade Tamper-Resistant Half-Controlled Plug Load Duplex Receptacle, Light Almond**  
Part No. TR5362CHLA



Permanent controlled receptacle marking allows for long-lasting, easy identification of controlled receptacle for end-users. NEMA-approved and compliant with NEC, CA Title 24, and ASHRAE Energy Efficiency Standard 90.1.

## Features & Benefits

Can be wired to any number of system-based or stand-alone plug load control solutions.	Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.
.032 inch thick, brass, triple-wipe power contacts for lasting retention.	Permanent controlled receptacle markings using abrasion resistant ink.
Two drive screws anchor strap to back body and face where abrupt removal torque is strongest.	Tri-drive brass-plated terminal screws. Two back-wire holes for more wiring flexibility.
Strap tabs wrap around face to prevent strap from separating from face and back body.	CH Version Only: Split circuit tab broken at the factory, allowing half of the receptacle to be controlled.
For covering patents, see <a href="http://www.legrand.us/patents">www.legrand.us/patents</a> .	

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Light Almond
UPC Number	785007051223	Country Of Origin	Mexico
Number of Receptacles	2	Outlet Type	Energy Saving On/Off, Tamper-Resistant
Application Sector	Commercial	Standard	FEDSPEC
Warranty Type	1-Year Limited Warranty	Type	Outlet

### Dimensions

Product Width US	1.322 in	Product Depth US	1.13 in
Product Height US	2.635 in		

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

### Technical Information

Amperage	20 A	Number of Poles	Double Pole
Indoor/Outdoor	Indoor		