



Pass and Seymour
3.1A Spec Grade USB Outlet, Type A, 20A, Tamper-Resistant, Ivory
Part No. TR5362USBI



Designed for commercial markets with strength and durability in mind, this combination USB charger duplex receptacle features 3.1A overall USB charging capability and is compatible with USB 2.0 & 3.0 devices. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

Overall 3.1A USB charging capability: Combination AC duplex receptacles include two 5-volt DC USB ports that work with USB 2.0 & 3.0 compatible devices.	One-piece heat-treated triple-wipe brass power contacts.
AC receptacles are tamper-resistant as standard: patented shutter system prevents improper insertion of foreign objects.	Multiple color options available.
Back and side wire terminals accommodate #14 AWG - #10 AWG stranded and solid copper wire.	Stainless steel auto-ground clips assure positive ground.
Wire Size: #14 - #10 AWG Copper Conductor Only	

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Finish	Matte	UPC Number	785007031584
Country Of Origin	Vietnam	Number of Receptacles	2
Features	USB-A Charging	Outlet Type	Tamper-Resistant, USB-Charging
Application Sector	Commercial	Standard	CSA Listed, cULus, FSUL, UL Listed, RoHS, FEDSPEC
Warranty Type	1-Year Limited Warranty	Type	Outlet

Dimensions

Product Width US	1.693 in	Product Depth US	1.392 in
Product Height US	2.677 in		

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Additional Information

Product Environmental Profile Yes

Technical Information

Dielectric Strength	Withstands 2000V minimum	Is Tamper-Resistant	Yes
USB Amperage	3.1 A	Number of USBs	2
USB Power Output	15 W	Temperature Rating	-40° - 60° C
Amperage	20 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor