



Tamper-Resistant Hospital Grade Receptacles, Smooth Face, Back and Side-Wire, 15A, 125A



## Features & Benefits

Thermoplastic dual mechanism shutter system to help prevent insertion of foreign objects.

Smooth face.

Exclusive patented feature, circuit label on face allows permanent circuit identification.

Extra heavy-duty brass, one-piece mounting strap with integral ground.

One-piece, nickel-plated brass, triple-wipe power contacts for lasting retention.

Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.

Impact-resistant nylon face and back body.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Two drive screws anchor strap to back body and face.

Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.

External screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.

Auto-ground clip assures positive ground.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.  
Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

## Specifications

### General Info

Product Line

Pass & Seymour

Color

Gray

|  |             |                    |             |
|--|-------------|--------------------|-------------|
| Country Of Origin                            | Mexico      | Application Sector | Commercial  |
| Standard                                     | UL 498      |                    |             |
| <b>Dimensions</b>                            |             |                    |             |
| Product Width US                             | 1.625 in    | Product Depth US   | 0.9 in      |
| Product Height US                            | 2.75 in     |                    |             |
| <b>Listing Agencies / 3rd Party Agencies</b> |             |                    |             |
| cULus ListingNumber                          | 140596      | cULus Listed       | Yes         |
| <b>Technical Information</b>                 |             |                    |             |
| Is Tamper-Resistant                          | Yes         | Phase              | 3           |
| Number of Wires                              | 3           | Amperage           | 15 A        |
| Number of Poles                              | Double Pole | Wire Size          | 14 - 10 AWG |
| Voltage                                      | 125.0 V     |                    |             |