



Hospital-Grade Tamper-Resistant Compact Design Receptacles, Back and Side Wire, 15A, 125V

Features & Benefits

- Impact-resistant nylon face.
- Easily accessible break-off line contact connecting tab for split circuit wiring.
- Internal screw-pressure-plate back wire and side wire line terminals accept #14 : #10 AWG copper or copper-clad conductors.
- Compact design for easy installation.
- Meets National Electrical Code Tamper-Resistant requirements.
- Stainless steel mounting screws also resist corrosion.
- Corrosion-resistant, zinc-plated steel strap is locked in.
- High strength thermoplastic back body.
- Tri-drive terminal and mounting screws.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	Light Almond
Country Of Origin	Mexico	Number of Receptacles	2
Outlet Type	Commercial, Indoor, Tamper-Resistant	Warranty Type	1-Year Limited Warranty
Type	Outlet		

Dimensions

Product Width US	1.322 in	Product Depth US	0.78 in
Product Height US	2.635 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Is Tamper-Resistant	Yes	Amperage	15 A
Number of Poles	Double Pole	Indoor/Outdoor	Indoor
Voltage	125.0 V		
