



Hospital-Grade Tamper-Resistant Compact Design Receptacles, Back and Side Wire, 15A, 125V

Features & Benefits

Impact-resistant nylon face.	Stainless steel mounting screws also resist corrosion.
Easily accessible break-off line contact connecting tab for split circuit wiring.	Corrosion-resistant, zinc-plated steel strap is locked in.
Internal screw-pressure-plate back wire and side wire line terminals accept #14 : #10 AWG copper or copper-clad conductors.	High strength thermoplastic back body.
Compact design for easy installation.	Tri-drive terminal and mounting screws.
Meets National Electrical Code Tamper-Resistant requirements.	For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here .

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007035230
Country Of Origin	Mexico	Number of Receptacles	2
Outlet Type	Tamper-Resistant	Application Sector	Commercial, Hospital Grade
Warranty Type	1-Year Limited Warranty	Type	Outlet

Dimensions

Product Width US	1.322 in	Product Depth US	0.78 in
Product Height US	2.635 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Is Tamper-Resistant	Yes	Amperage	15 A
---------------------	-----	----------	------

Number of Poles	Double Pole	Indoor/Outdoor	Indoor
-----------------	-------------	----------------	--------
