



Pass and Seymour  
Discontinued - 15A Extra Heavy Duty Power Indicating Hospital-Grade Receptacle, White  
Part No. TR8200PIW



Built for the harshest medical environments, P&S power indicating receptacles feature two industry-exclusive green LEDs that offer clear visual assurance of power indication at the receptacle—even with critical equipment plugged into the device. The LEDs operate independently from one another to accommodate split-circuit wiring installations. Tamper-resistant protection comes standard with each receptacle to further enhance safety.

## Features & Benefits

Thermoplastic dual mechanism shutter system to help prevent insertion of foreign objects.

Extra heavy-duty brass, one-piece mounting strap with integral ground.

Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Exclusive patented feature, circuit label on face allows permanent circuit identification.

One-piece, nickel-plated: brass, triple-wipe power contacts for lasting retention.

Impact-resistant nylon face and back body.

Two drive screws anchor strap to back body and face.

External screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Wire Size: #14 - #10 AWG Copper Conductor Only

## Specifications

### General Info

|                   |                             |                    |                |
|-------------------|-----------------------------|--------------------|----------------|
| Product Line      | Pass & Seymour              | Color              | White          |
| Country Of Origin | Mexico                      | Application Sector | Hospital Grade |
| Standard          | CSA Listed, UL Listed, FSUL |                    |                |

### Listing Agencies / 3rd Party Agencies

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

|                     |                          |                          |             |
|---------------------|--------------------------|--------------------------|-------------|
| Dielectric Strength | Withstands 2000V minimum | Phase                    | Single      |
| Connection          | Side & Back Wired        | Number of Wires          | 3           |
| Temperature Rating  | -40° - 60° C             | Amperage                 | 15 A        |
| Number of Poles     | Double Pole              | Wire Size                | 14 - 10 AWG |
| Voltage             | 125.0 V                  | Environmental Conditions | UL94 V2     |