



15A Tamper-Resistant HG 2.1A USB Charging Receptacle

Features & Benefits

2.1 A USB type A receptacle charges faster than other USB receptacles eliminates the need for bulky AC adapters.

Back and side wire terminals accommodates #14 AWG - #10 AWG stranded and solid wire.

Stainless steel auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents.

Compact Design Tamper-Resistant receptacle and two 5-volt DC USB ports that work with USB 2.0 & 3.0 compatible devices.

Tamper-Resistant, patented shutter system prevents improper insertion of foreign objects. Meets 2011 National Electrical Code: Tamper-Resistant requirements.

Zink-plated ground terminal screw

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	TR8200HUSBW
Color	White	UPC Number	785007030310
Country Of Origin	China		

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

USB Amperage	2.1 A	USB Power Output	11 W
--------------	-------	------------------	------

Amperage

15 A
