



Pass and Seymour

20A 125V Hospital-Grade Tamper-Resistant Compact Duplex Receptacle, Back and Side Wire, Black

Part No. TR8300HBK



Hospital-Grade Tamper-Resistant Compact Design Receptacle, Back and Side Wire, 20A, 125V

## Features & Benefits

Impact-resistant nylon face.

Stainless steel mounting screws also resist corrosion.

Easily accessible break-off line contact connecting tab for split circuit wiring.

Corrosion-resistant, zinc-plated steel strap is locked in.

Internal screw-pressure-plate back wire and side wire line terminals accept #14 : #10 AWG copper or copper-clad conductors.

High strength thermoplastic back body.

Compact design for easy installation.

Tri-drive terminal and mounting screws.

Meets National Electrical Code Tamper-Resistant requirements.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Wire Size: #14 - #10 AWG Copper Conductor Only

## Specifications

### General Info

|                   |                                      |                       |                         |
|-------------------|--------------------------------------|-----------------------|-------------------------|
| Product Line      | Pass & Seymour                       | Color                 | Black                   |
| Country Of Origin | Mexico                               | Number of Receptacles | 2                       |
| Outlet Type       | Commercial, Indoor, Tamper-Resistant | Warranty Type         | 1-Year Limited Warranty |
| Type              | Outlet                               |                       |                         |

### Dimensions

---

Product Width US 1.322 in

Product Depth US 0.78 in

---

Product Height US 2.635 in

---

### Listing Agencies / 3rd Party Agencies

---

cULus Listed Yes

---

### Technical Information

---

Is Tamper-Resistant Yes

Amperage 20 A

---

Number of Poles Double Pole

Indoor/Outdoor Indoor

---

Voltage 125.0 V

---