



Pass and Seymour
Tamper-Resistant Hospital Grade Extra Heavy Duty Surge Protective Duplex Receptacle, White
Part No. TR8300WSP



Tamper-Resistant Hospital Grade Extra Heavy-Duty Surge Protective Duplex Receptacle offers increased transient protection, reliability and protection notification (Audible Alarm with LED Indicator). Back and Side Wire, 20amp 125volt, Blue. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

Dual mechanical shutter system to help prevent insertion of foreign objects.	Auto-ground clip assures positive ground.
Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.	Backed-out tri-drive brass terminal screws for faster installation.
Internal screw-pressure-plate back and side wire capability.	Two back wire holes for additional wiring flexibility.
Corrosion-resistant plated steel strap is locked in to face and back body to resist pulling away from the face/body assembly.	.032 inch thick brass triple-wipe power contacts.
Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest.	For covering patents, see www.legrand.us/patents .

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007019995
Country Of Origin	China	Application Sector	Commercial, Residential

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Phase	Single	Connection	Side & Back Wire
Class	IG	Amperage	20 A
Type of Indicators	Audible Alarm, LED	Environmental Conditions	UL94 V2