



Pass and Seymour

Discontinued - USB Charger with Hospital Grade Tamper-Resistant Single Receptacle, White

Part No. TR8301USBW



2 Standard type A USB's, 2.1 A or 2100mA, 10.5 watts. Combination with Hospital Grade Tamper-Resistant 20 A AC Single Receptacle, White.

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles page](#).

Features & Benefits

2.1 A USB type A receptacle charges faster than other USB receptacles eliminates the need for bulky AC adapters.

Compact Design Tamper-Resistant receptacle and two 5-volt DC USB ports that work with USB 2.0 & 3.0 compatible devices.

Back and side wire terminals accommodates #14 AWG - #10 AWG stranded and solid wire.

Tamper-Resistant, patented shutter system prevents improper insertion of foreign objects. Meets 2011 National Electrical Code: Tamper-Resistant requirements.

Stainless steel auto-ground clip assures positive ground.

Zink-plated ground terminal screw

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	TR8300HUSBW
Color	White	Country Of Origin	China

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Is Tamper-Resistant	Yes	USB Amperage	2.1 A
USB Power Output	11 W	Amperage	20 A