



Pass and Seymour

Tamper-Resistant Isolated Ground Heavy-Duty Spec Grade Receptacles, Light Almond

Part No. TRIG5362LA



Tamper-Resistant Isolated Ground Heavy-Duty Spec Grade Duplex Receptacle, Back & Side Wire, 20amp 125volt, Orange. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

Dual mechanical shutter system to help prevent insertion of foreign objects.

Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.

Internal screw-pressure-plate back and side wire capability.

Corrosion-resistant plated steel strap is locked in to face and back body to resist pulling away from the face/body assembly.

Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Auto-ground clip assures positive ground.

Backed-out tri-drive brass terminal screws for faster installation.

Two back wire holes for additional wiring flexibility.

.032 inch thick brass triple-wipe power contacts.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

UPC Number	785007011890	Country Of Origin	Mexico
Product Line	Pass & Seymour	Application Sector	Commercial
Standard	cULus UL498		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	cULus ListingNumber	140596
--------------	-----	---------------------	--------

Technical Information

Number of Poles	Double Pole	Voltage	125 V
Connection	Back and side wire	Dielectric Strength	Withstands 2000V minimum
Temperature Rating	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact	Wire Size	#14 - #10
Number of Wires	3	Environmental Conditions	Flammability: UL94 V2

