



Pass and Seymour
Discontinued - Tamper-Resistant Hospital Grade Isolated Ground Surge Protective Duplex Receptacle, Blue
Part No. TRIG8200BLSP



Features & Benefits

| | |
|---|--|
| Dual mechanical shutter system to help prevent insertion of foreign objects. | Auto-ground clip assures positive ground. |
| Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring. | Backed-out tri-drive brass terminal screws for faster installation. |
| Internal screw-pressure-plate back and side wire capability. | Two back wire holes for additional wiring flexibility. |
| Corrosion-resistant plated steel strap is locked in to face and back body to resist pulling away from the face/body assembly. | .032 inch thick brass triple-wipe power contacts. |
| Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest. | For covering patents, see www.legrand.us/patents . |

Specifications

General Info

| | | | |
|--------------------|------------------------|-------------------|-------|
| Product Line | Pass & Seymour | Country Of Origin | China |
| Application Sector | Residential/Commercial | | |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

| | | | |
|------------|------------------|--------------------------|--------------------|
| Phase | Single | Frequency Rating | 60 Hz |
| Connection | Side & Back Wire | Class | IG |
| Amperage | 15 A | Type of Indicators | LED, Audible Alarm |
| Voltage | 125.0 V | Environmental Conditions | UL94 V2 |