



Pass and Seymour
TradeMaster® 0-10V Fluorescent/LED Single Pole/3-Way Toggle Slide Dimmer, Preset, Red
Part No. TSD4FBL3PRED



TradeMaster® Toggle Slide Dimmer offers a solution for your residential LED or fluorescent lighting needs. This single pole 3-way switch can be used in a two-location layout. The slide can be set to your preferred level and then toggle on and off providing instant repeatability.

Features & Benefits

Matches appearance of standard Pass and Seymour toggle switch
Interchangeable face covers are available in seven different colors
Lifetime warranty

All models are Single Pole/3-Way capable
Highest wattage rating

Specifications

General Info

| | | | |
|--------------------|--------------------------------------|--------------------|--|
| Product Line | Pass & Seymour | Color | Red |
| Finish | Gloss | UPC Number | 785007216967 |
| Country Of Origin | China | Features | Color Change Kit, Low-End Trim (Dim Range) |
| Switch Type | Single Pole 3-Way, Slider, Toggle | Number of Switches | 1 |
| Application Sector | Commercial, Hospitality, Residential | Warranty Type | Limited Lifetime Warranty |

Dimensions

| | | | |
|-------------------|---------|------------------|--------|
| Product Width US | 1.73 in | Product Depth US | 1.4 in |
| Product Height US | 4.19 in | | |

Technical Information

| | | | |
|-----------------------|-------------------|-----------------------|--|
| Preset | Yes | Load Rating | 120V 10A (Fluorescent), 120V 10A (LED), 277V 5A (Fluorescent), 277V 5A (LED) |
| Dimming Compatibility | 0-10 V | Frequency Rating | 60 Hz |
| Number of Gangs | 1 | Bulb Compatibility | Fluorescent, LED |
| Number of Poles | Single Pole 3-Way | Wire Size | #14 - #10 AWG |
| Trim/Adjustment Level | Wheel | Requires Neutral Wire | No |
| Indoor/Outdoor | Indoor | Mounting Type | Wall Box |
| Wire Connection Type | Flying Leads | Voltage | 120/277 VAC |