



Pass and Seymour
TradeMaster® Tru-Universal Single Pole/3-Way Toggle Slide Dimmer, Preset, Red
Part No. TSD703PTURED



TradeMaster® Toggle Slide Tru-Universal Dimmer is designed for use with virtually any lamp type. This single pole 3-way switch is compatible with incandescent, halogen, ELV, CFL, or LED lighting options and can be used in a two-location layout. The slide can be set to your preferred level and then toggle on and off providing instant repeatability.

Features & Benefits

Matches appearance of standard Pass and Seymour toggle switch

Interchangeable face covers are available in seven different colors

Lifetime warranty

All models are Single Pole/3-Way capable

Highest wattage rating

Specifications

General Info

Product Line	Pass & Seymour	Color	Red
Finish	Gloss	UPC Number	785007216660
Country Of Origin	China	Features	Auto-Calibration (Trim), Color Change Kit, High-End Trim (Dim Range), Low-End Trim (Dim Range)
Switch Type	Single Pole 3-Way, Slider, Toggle	Number of Switches	1
Application Sector	Commercial, Hospitality, Residential	Warranty Type	Limited Lifetime Warranty

Dimensions

Product Width US	1.73 in	Product Depth US	1.4 in
Product Height US	4.19 in		

Technical Information

Preset	Yes	Load Rating	120V 4.5A 450W (CFL), 120V 4.5A 450W (LED), 120V 5.5A (EFL), 120V 500VA (MLV), 120V 700W (ELV), 120V 700W (Halogen), 120V 700W (Incandescent)
Dimming Compatibility	Forward or Reverse Selectable Phase	Frequency Rating	60 Hz
Number of Gangs	1	Bulb Compatibility	CFL, Fluorescent, Halogen, Incandescent, LED
Number of Poles	Single Pole 3-Way	Wire Size	#14 - #10 AWG
Trim/Adjustment Level	Button with Slider	Requires Neutral Wire	Yes
Indoor/Outdoor	Indoor	Mounting Type	Wall Box
Wire Connection Type	Screw Terminals	Voltage	120 VAC