



Pass and Seymour  
TradeMaster® LED/CFL/Incandescent Single Pole/3-Way Toggle Slide Dimmer, Preset, Black  
Part No. TSDCL303PBK



TradeMaster® Toggle Slide Dimmer is designed for use with compact fluorescent or LED lighting fixtures. This single pole 3-way switch can be used in a two-location layout. The slide can be set to your preferred level and then toggle on and off providing instant repeatability.

This switch offers dependability and a lifetime warranty.

## Features & Benefits

Matches appearance of standard Pass and Seymour toggle switch  
Interchangeable face covers are available in seven different colors  
Lifetime warranty

All models are Single Pole/3-Way capable  
Highest wattage rating

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	China	Switch Type	Rocker, Slider
Number of Switches	1	Warranty Type	Limited Lifetime Warranty

### Dimensions

Product Width US	2.5 in	Product Depth US	1.4 in
Product Height US	4.19 in		

### Technical Information

Amperage	2.5 A	Bulb Compatibility	CFL, Incandescent, LED
Number of Poles	3-Way, Single Pole	Wattage	700 W
Voltage	120.0 V		